

**8791**

**Open end fitting**

**16 Z**





- For accessing bolts in cramped and hard-to-access locations - easy to change
- Forged
- Chrome-vanadium steel, chrome-plated
- With eject-pin for unlocking



Code	No.	Ø	mm	mm	mm	Depth gauge	mm
7774470	<b>8791-07</b>	16	7	5	20.5	32	80
7774550	<b>8791-08</b>	16	8	5	20.5	32	80
7774630	<b>8791-09</b>	16	9	5	20.5	32	80
7710070	<b>8791-10</b>	16	10	7	29.0	32	90
7710150	<b>8791-11</b>	16	11	7	29.0	32	90
7676890	<b>8791-12</b>	16	12	7	29.0	32	90
7710230	<b>8791-13</b>	16	13	8	34.5	32	120
7710310	<b>8791-14</b>	16	14	8	34.5	32	120

Code	No.	Ø	mm	mm	mm	Depth gauge	
7710580	<b>8791-15</b>	16	15	8	34.5	32	120
7710660	<b>8791-16</b>	16	16	9	41.5	32	160
7710740	<b>8791-17</b>	16	17	9	41.5	32	160
7676970	<b>8791-18</b>	16	18	9	41.5	32	160
7710820	<b>8791-19</b>	16	19	10	45.0	32	180
7710900	<b>8791-20</b>	16	20	10	45.0	32	180
7677000	<b>8791-21</b>	16	21	10	45.0	32	180
7711040	<b>8791-22</b>	16	22	11	56.0	32	220
7711120	<b>8791-24</b>	16	24	11	56.0	32	220
7711200	<b>8791-27</b>	16	27	12	60.5	32	260
7774710	<b>8791-30</b>	16	30	12	68.0	32	300
7774980	<b>8791-32</b>	16	32	12	68.0	32	300
1552317	<b>8791-36</b>	16	36	12	68.0	32	300

Code	No.	Ø	AF	mm	mm	Depth gauge	
1211421	<b>8791-1/4AF</b>	16	1/4	5	20.5	32	90
7720030	<b>8791-5/16AF</b>	16	5/16	5	20.5	32	80
1211447	<b>8791-3/8AF</b>	16	3/8	7	29.0	32	90
7720110	<b>8791-7/16AF</b>	16	7/16	7	29.0	32	90
7720380	<b>8791-1/2AF</b>	16	1/2	8	34.5	32	90
7720460	<b>8791-9/16AF</b>	16	9/16	8	34.5	32	120
7720540	<b>8791-5/8AF</b>	16	5/8	9	41.5	32	160
7720620	<b>8791-11/16AF</b>	16	11/16	9	41.5	32	160
7720700	<b>8791-3/4AF</b>	16	3/4	10	45.0	32	180
1211439	<b>8791-13/16AF</b>	16	13/16	10	45.0	32	90

Code	No.	Ø	 AF	mm 	 mm	Depth gauge	
7720890	<b>8791-7/8AF</b>	16	7/8	10	45.0	32	220
7720970	<b>8791-15/16AF</b>	16	15/16	11	56.0	32	220
7721000	<b>8791-1AF</b>	16	1	11	56.0	32	220
7721190	<b>8791-1.1/16AF</b>	16	1.1/16	12	60.5	32	260
7721270	<b>8791-1.1/8AF</b>	16	1.1/8	12	68.0	32	300
7776170	<b>8791-1.3/16AF</b>	16	1.3/16	12	68.0	32	300
7776250	<b>8791-1.1/4AF</b>	16	1.1/4	12	68.0	32	300
7776330	<b>8791-1.5/16AF</b>	16	1.5/16	12	68.0	32	300