

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153452125](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Squba 3.6 Female-to-Squba 3.6 Female, Tin (Sn) Plating, 450.00mm Length, 16 AWG, Red

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	215345
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Squba
UPC	195842349407

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Modified Polystyrene
Net Weight	7.090/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm-2.40mm
Wire Size AWG	16
Wire/Cable Type	UL 11028

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Sales Drawing	2153451121-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[215345 Series](#)