



Nitrotough™ CR270, CR350, CR400



3121



JKL



CE Complex Design



APPLICATIONS

Ideal for chemical and general handling even in oily conditions.

FEATURES AND BENEFITS

Nitrile coated liquid proof gauntlet

Exceptional electrical properties as the finished material offers the user hand protection against static discharge

High abrasion resistance

Gauntlet style offers the same level of protection from finger tip to cuff

21CRF (USA) compliant for food applications

Available in 270mm (CR270), 350mm (CR350) and 400mm (CR400) lengths.

Size	Order code
CR270	
7 (S)	9999212
8 (M)	9999213
8 (L)	9999214
10 (XL)	9999215
Length 270 mm	
CR350	
7 (S)	9999216
8 (M)	9999217
8 (L)	9999218
10 (XL)	9999219
Length 350 mm	
CR400	
7 (S)	9999220
8 (M)	9999221
8 (L)	9999222
10 (XL)	9999223
Length 400 mm	



Multiplus



4121



AKL



CE Complex Design



APPLICATIONS

Ideal for tasks involving mechanical and chemical hazards: maintenance, cleaning, petrochemical plants, factories.

FEATURES AND BENEFITS

Supported PVC formulation glove with double-dip granite finish

100% cotton interlock liner

Excellent resistance to chemical destruction, offering protection against cutting oil, petrol and by-products, bases, acids, including those in the solvent

Anatomical shape for increased dexterity and comfort

Excellent resistance to abrasion and tear.

Size	Order code
Multiplus 27	
8	0314E02
9	0314E03
10	0314E04
11	0314E00
Length 270 mm	
Multiplus 40	
8	0317E02
9	0317E03
10	0317E04
11	0317E00
Length 400 mm	



Long Nitrosolve™ Z51G



4102



CE Complex Design



APPLICATIONS

Ideal for use in chemical, automotive, printing and petroleum related industries.

FEATURES AND BENEFITS

Nitrile formula for resistance to many solvents and oil based chemicals

Effective resistance to most solvents, oils, fats and greases

A tough chemical resistant glove with long elbow length cuff for extra protection

High abrasion and puncture resistance.

Flock lined for greater comfort during use.

Size	Order code
8 (M)	03884
9 (L)	03885
10 (XL)	03886
Length 440 mm	
Thickness (double wall) 1.12 mm	