



product details

## HQI-T 250W/N/SI E40 FS1



Product description: HQI-T 250W/N/SI E40 FS1  
 EAN/ Product: 4050300444604  
 Quantity: Folding carton box (FS) contains 1 Piece (PCE)

You can find this product in the eCatalog:  
[http://catalog.myosram.com?~language=EN&~country=COM&it\\_p=4050300444604](http://catalog.myosram.com?~language=EN&~country=COM&it_p=4050300444604)

Applications	
Burning position	any

General Description	
ILCOS	MT-250/37/2B-H 133/S-E40-57.2/248
SEG no.	8333080
Sstl-Number	4834707
Base (standard designation)	E40

Technical - Electrical Data	
PFC capacitor at 50 Hz	32 $\mu$ F <sup>1)</sup>
Construction wattage	250 W
Nominal wattage (packaging)	250 W

Technical - Geometries	
Light centre length (LCL)	160 mm
Length	248 mm
Diameter	57 mm

Technical - Life	
Lifespan	12000 h <sup>2)</sup>

Technical - Light Technical Data	
Colour temperature	3700 K
Colour rendering group	2B
Colour rendering index Ra	60 ... 69
Luminous efficacy	78 lm/W
Luminous flux	20000 lm

Packaging units				
EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4050300444604	Folding carton box contains 1 Piece	0,000 mm x 0,000 mm x 0,000 mm	0,000 g (210,000 g)	0,000 Cubic dec.
4050300444611	Shipping carton box contains 10 Piece	170,000 mm x 300,000 mm x 350,000 mm	2,300 kg (2,100 kg)	17,850 Cubic dec.

1) at rated voltage and  $\cos \varphi \geq 0.9$

2) Average lifespan