

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1731120409](#)  
**Status:** **Active**  
**Overview:** [FCT D-Sub Connectors](#)  
**Description:** FCT Stamped Contact, Male, Crimp, 0.80µm Gold Plating, 20-24 AWG

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	D-Sub Products
Series	<a href="#">173112</a>
Contact Type	Stamped Crimp
Overview	<a href="#">FCT D-Sub Connectors</a>
Product Category	Contacts
Product Name	FCT Products
Type	Standard Density
UPC	191128209687

**Physical**


Durability (mating cycles max)	500
Gender	Male
Material - Contact	Copper Alloy
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Reel
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Temperature Range - Operating	-55° to +125°C
Termination Style	Crimp
Wire Size AWG	20, 22, 24

**Electrical**

Current - Maximum per Contact	5.0A
-------------------------------	------

**Material Info**

Engineering Number	P7LSR-K176
--------------------	------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[173112 Series](#)

**Use With**

FCT Standard-Density Connectors