

## Pen-Type Multimeter with Voltage Detect



- 1999 count LCD display
- Auto or manual ranging
- Audible and visual non-contact voltage detection
- Continuity and diode test
- Data and MAX hold
- Auto power off
- Safety Category: IEC1010-1 CATIII 600V

Function	Max. Range	Basic Accuracy
DC Voltage	600V	$\pm(0.7\%+2d)$
AC Voltage	600V	$\pm(0.8\%+3d)$
Resistance	20M $\Omega$	$\pm(1.0\%+1d)$

### Physical Specifications

Power	2x AAA batteries
Dimensions (WxHxD)	38 x 208 x 29mm
Weight	110g

**Includes:** soft carry case/holster, probe test lead and alligator test lead.

**Order Code**

**133-9600**