

SDIS 0.4X2.0X60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm
Order No.	2749780000
Type	SDIS 0.4X2.0X60
GTIN (EAN)	4050118896527
Qty.	1 Stück

Erstellungs-Datum October 22, 2021 8:26:55 AM CEST

Katalogstand 08.10.2021 / Technische Änderungen vorbehalten

SDIS 0.4X2.0X60

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Width	164 mm	Width (inches)	6.457 inch
Net weight	40 g		

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.4 x 2.0 x 60
------------------------	---

Screwing tools

Blade length	60 mm	Blade thickness (A)	0.4 mm
Blade type	A	Blade width (B)	2 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07		

Downloads

Catalogues	Catalogues in PDF-format
------------	--