


Aluminium Standard – 01.06 19 00

Aluminium enclosure consisting of lid, seal, incl. captive +/-stainless steel screws, base with 2 or 4 earthing screws



Dimensions H x W x D (mm)	64 x 185 x 34
Weight (g)	360
Order number	01.06 19 00
Product type	ALS 01035

- + Robust aluminium enclosure for mechanical engineering and automation technology
- + Fixing options for DIN rails and mounting plates
- + Usable in wide temperature area




Technical Data

Material	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Powder coating, RAL 7001, silver grey, special colour on request
Ingress protection	IP 66 to EN 60529, higher protection on request
Impact resistance	7 Joule in reference to EN 60079-0
Temperature range	PU (polyurethane) seal (std.): -40°C to +90°C CR (chloroprene) seal: -40°C to +100°C VMQ (silicone) seal (optional): -60°C to +130°C
Other versions on request	EMC, SBG, SBGL, SWB, Silicone lid seal

Aluminium Standard – 01.06 19 00

Number of cable glands

Maximum number of cable glands to DIN 50262*



M	PG	Side	
		A/B	C/D
12	17,25	10	1
16	25,30		
20	27,60		
25	37,95		
32	48,30		
40	60,95		
50	69,00		
63	74,75		
75			
85			

Commercial Data

Country of origin	IN
Pieces per packaging	1
Customs tariff number	85369095
Weight (g)	360
GTIN	4250157900067

ETIM Classification

ETIM-Class	EC000058
------------	----------

Accessories

Description	Order number
Allen lid screws	12.01 80 02
Lead-sealing screw	12.01 90 01