



Push mounts require no adhesive backing or additional mounting hardware. They are inserted into pre-drilled holes. Can be used where only one side of the panel is accessible. This push mount does not have tensioning wings.

Part Number:	PM2H25-C
Product Family:	Push Mounts
Product Line:	Push/Tree Barb
RoHS Compliancy Status:	Compliant
Part Description:	Push Barb Cable Tie Mount
Product Type:	Cable Tie Mounts - Push Mount
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Height (In.):	.18
Height (mm):	4.6
Width (In.):	.38
Width (mm):	9.6
CE Compliant:	CT-ACC4 / 10.96
Environment:	Indoors
Flammability Rating:	UL94 V-2
Max. Panel Thickness (In.):	.125
Max. Panel Thickness (mm):	3.2
Mounting Method:	Push Barb
Panel Hole Diameter (In.):	.250
Panel Hole Diameter (mm):	6.4

