



This clamp provides a fast and convenient method of securing bundles from .19" (4.8mm) up to .69" (17.5mm) diameter. It is available with adhesive backing or screw applied with one #6 (M3) screw.

Part Number: ARC.68-A-Q14
Product Family: *Clincher*TM Adjustable Releasable Clamp
Product Line: Adhesive Backed

Product Line: Adhesive Mounts

RoHS Compliancy Status: Compliant

Part Description: Adjustable and Releasable Clamp

Product Type: Wire Mounting Clamp

Material: Polypropylene

Color: Gray

UL Recognized: E136577

Length (In.): 1.00
Length (mm): 25.4

Width (In.): 1.00
Width (mm): 25.4

Adhesive Type: Rubber

Bundle Diameter Range (In.): .19-.69
Bundle Diameter Range (mm): 4.8-17.5

Environment: Indoors

Max. Bundle Diameter (In.): .68
Max. Bundle Diameter (mm): 17.5

Max. Static Load (g): 227

