



Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

Part Number: FCM1.2-A-C14

Product Family: Latching Flat Cable Mounts

Product Line: Flat/Ribbon Cable

RoHS Compliancy Status: Compliant

Part Description: Adhesive Backed Latching Flat Cable Holder

Product Type: Mounting Device

Material: Nylon 6.6

Color: Gray

UL Recognized: E136577

Length (In.): 3.16

Length (mm): 80.3

Width (In.): 1.00

Width (mm): 25.4

Adhesive Type: Rubber adhesive

Cable Width (In.): 1.20

Cable Width (mm): 30.5

Environment: Indoors

Max. Flat Cable Width (In.): 1.20

Max. Flat Cable Width (mm): 30.5

Max. Static Load (g): 281

Max. Static Load (Lbs.): .62

Metric Screw Size: M3

Mounting Method: Rubber adhesive

Screw Size: #6 (M3)

Std. Pkg. UOM: PK

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100