



Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

Part Number: FCM3.25-A-L14

Product Family: Latching Flat Cable Mounts

Product Line: Flat/Ribbon Cable

RoHS Compliancy Status: Compliant

Part Description: Adhesive Backed Latching Flat Cable Holder

Product Type: Mounting Device

Material: Nylon 6.6

Color: Gray

UL Recognized: E136577

Length (In.): 7.30

Length (mm): 185.4

Width (In.): 1.00

Width (mm): 25.4

Adhesive Type:	Rubber adhesive
Cable Width (In.):	3.38
Cable Width (mm):	85.9
Environment:	Indoors
Max. Flat Cable Width (In.):	3.25
Max. Flat Cable Width (mm):	82.6
Max. Static Load (g):	681
Max. Static Load (Lbs.):	1.50
Metric Screw Size:	M3
Mounting Method:	Rubber adhesive
Open Length (In.):	7.3
Open Length (mm):	185.4
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50