



Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

Part Number: FCM1-S6-C14
Product Family: Latching Flat Cable Mounts
Product Line: Flat/Ribbon Cable

RoHS Compliancy Status: Compliant

Part Description: Adhesive Backed Latching Flat Cable Holder

Product Type: Mounting Device

Material: Nylon 6.6

Color: Gray

UL Recognized: E136577

Length (In.): 1.21

Length (mm): 30.7

Width (In.): 1.00

Width (mm): 25.4

Cable Width (In.):	1.06
Cable Width (mm):	26.7
Environment:	Indoors
Flammability Rating:	UL94 V-2
Max. Flat Cable Width (In.):	1.00
Max. Flat Cable Width (mm):	25.4
Metric Screw Size:	M3
Mounting Method:	#6 (M3) Screw
Open Length (In.):	2.90
Open Length (mm):	73.7
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100