



Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

Part Number: FCM1.2-S6-C14

Product Family: Latching Flat Cable Mounts

Product Line: Flat/Ribbon Cable

RoHS Compliancy Status: Compliant

Part Description: Adhesive Backed Latching Flat Cable Holder

Product Type: Mounting Device

Material: Nylon 6.6

Color: Gray

UL Recognized: E136577

Length (In.): 1.37

Length (mm): 34.8

Width (In.): 1.20

Width (mm): 30.5

| | |
|------------------------------|---------------|
| Cable Width (In.): | 1.21 |
| Cable Width (mm): | 30.7 |
| Environment: | Indoors |
| Flammability Rating: | UL94 V-2 |
| Max. Flat Cable Width (In.): | 1.00 |
| Max. Flat Cable Width (mm): | 30.5 |
| Metric Screw Size: | M3 |
| Mounting Method: | #6 (M3) Screw |
| Open Length (In.): | 3.16 |
| Open Length (mm): | 80.3 |
| Screw Size: | #6 (M3) |
| Std. Pkg. UOM: | PK |
| UOM: | PC |
| Std. Pkg. Qty.: | 100 |
| Min. Order Qty.: | 100 |