

TECHNICAL DATA SHEET

Part#: 7240E

Cutters - Medium Oval Head - Semi-Flush - Short Handle Designed for maximum tool life, cutting up to .050" diameter soft wire

The 7240E Lazer Line® medium oval semi-flush cutter has a cutting capacity of .008" - .050" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action. It features a ergonomically molded antimicrobial Anti-Static grip (10¹⁰ ohms/sq surface resistivity) with dual leaf springs.

Precision Level

Material

Surface Resistivity

Shape

Type of Cut

Cutting Capacity

Blade Angle

Blade Length

Body Width

Body Height

• OAL

Weight (OZ)

UPC

Schedule B

• ECCN

• UNSPSC Code

Country of Origin

Group

Carbon

10¹⁰ ohms/sq

Round Head

Semi-Flush

.008 - .050"

14.25°

.38" (9.5mm)

0.42" (10.5mm)

.25"

4.75" (118.75mm)

662847009488

8203.20.60.60

EAR99

27111511

USA

Medium Cutters - 7000 Series









