



- Funnel entry design for fast insertion of wires and cables
- Available in vertical and horizontal loading configurations
- Design of wing provides added stability

Part Number:	VWS4238-C
Product Family:	Wire Saddles
Product Line:	Push Mounts
Product Line:	Push/Tree Barb
Product Line:	Wire & Network Saddles
RoHS Compliancy Status:	Compliant
Part Description:	Vertical Entry Wire Saddle
Product Type:	Mounting Device
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Height (In.):	.78

Height (mm):	19.8
Width (In.):	.60
Width (mm):	15.2
Environment:	Indoors
Flammability Rating:	UL94 V-2
Max. Bundle Capacity (In.):	.40 x .42
Max. Bundle Capacity (mm):	10.0 x 11.0
Max. Panel Thickness (In.):	.08
Max. Panel Thickness (mm):	2.0
Mounting Method:	Push Barb
Panel Hole Diameter (In.):	.19
Panel Hole Diameter (mm):	4.7
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100