



For retaining wires, cable, components or tubing away from panel or conductive chassis. Finger grip flanges can be easily locked or unlocked for revisions. Hand installed in pre-drilled hole.

Part Number: WS50-75-C
Product Family: Wire Standoffs
Product Line: Push/Tree Barb

RoHS Compliancy Status: Compliant

Part Description: Push Barb Wire Standoff Clip

Product Type: Mounting Device

Material: Nylon 6.6

Color: Natural

UL Recognized: E136577

Environment: Indoors

Flammability Rating: UL94 V-2

Max. Bundle Diameter (In.): .47

Max. Bundle Diameter (mm):	11.9
Max. Panel Hole Diameter Range (In.):	.19 - .20
Max. Panel Hole Diameter Range (mm):	4.7 - 4.9
Max. Panel Thickness (In.):	.08
Max. Panel Thickness (mm):	2.0
Mounting Method:	Push Barb
Panel Hole Diameter (In.):	.187
Panel Hole Diameter (mm):	4.7
Standoff Height (In.):	.75
Standoff Height (mm):	19.1
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100