


# Display Port Male

# Display Port Male




**Note:**

- Source Resolution UXGA:  
7680x4230 @60Hz  
3480x2160 @120HZ

Part No.	Length	Resistance
11.04.5866	1000 mm	2 ohm
11.04.5867	2000 mm	2 ohm

**Specification :**

- |                  |  |
|------------------|--|
| 1. Cable         | UL20276, [(1P(30AWG)+D+AL/MY)*5 + 4C(30AWG)] + AL/MY +BD,<br>OD: 6.3±0.15mm, Jacket: Black PVC with Cotton Braid |
| 2. Conn.         | DisplayPort Male, Conductor: Gold Plated, Shell: Gold Plated   |
| 3. Hood          | For DisplayPort, ABS, Color: Gray  |
| 4. Inner Molding | PE   |
| 5. S.R.          | PVC: 45P, Color: Black   |



<b>SECOMP</b>	Product Name	ROLINE Silver DisplayPort Cable v1.4, M/M	Approve	Check	Draw	Design	Rev.	Date	Contents of Change	Design
	Product No.	11.04.5866 / 11.04.5867	<i>Allen</i>	<i>Allen</i>	<i>Kuan</i>	<i>Kuan</i>	1			
Issue Date : 2020/11/05				Scale 1:1	Unit : mm		2			
							3			