


Display Port Male

Display Port Male




Note:

- Source Resolution UXGA:
7680x4230 @60Hz
3480x2160 @120HZ

Part No.	Length	Resistance
11.04.5868	3000 mm	2 ohm

Specification :

- | | |
|------------------|--|
| 1. Cable | UL20276, [(1P(28AWG)+D+AL/MY)*5 + 4C(28AWG)] + AL/MY +BD,
OD: 7.3±0.15mm, Jacket: Black PVC with Cotton Braid |
| 2. Conn. | DisplayPort Male, Conductor: Gold Plated, Shell: Gold Plated |
| 3. Hood | For DisplayPort, ABS, Color: Gray |
| 4. Inner Molding | PE |
| 5. S.R. | PVC: 45P, Color: Black |



SECOMP	Product Name	ROLINE Silver DisplayPort Cable v1.4, M/M, 3m	Approve	Check	Draw	Design	Rev.	Date	Contents of Change	Design
	Product No.	11.04.5868	Allen	Allen	Kuan	Kuan	1			
Issue Date : 2020/11/05							2			
							3			

Scale 1:1 Unit : mm