




ELECTRICAL TEST:
 1.100% OPEN SHORT MIS WIRE TEST
 2.CONTACT RESISTANCE:5 OHM MAX
 3.INSULATION RESISTANCE:5M OHM MIN
 4.HI-POT TEST:DC 300V/10ms
 5.PASS 4K@60HZ TEST

CONSUMER ITEM	LENGTH (mm)
1M	1000±30
1.5M	1500±30
2M	2000±30
3M	3000±30



PIN Assignment

DP M DP M



⑤	CABLE	(1/0.254BC*1P+1/0.254TCCS+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*4C+Filler+AL-Foil+144#/0.12AL BLACK PVC Jacket OD:6.3±0.15mm	m
④	SHELL	Black ABS SHELL	2PCS
③	MODEL	Black 45P PVC	g
②	MODEL	PE,Nature color	g
①	plug	DP M 20P PIN:G/F,SHELL: Gold plated	2PCS
NO.	PART NAME	DESCRIPTION	QTY

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△	2021/07/09		A2
		YAN	YAN	FINISHING		△	2021/06/10		A1
				MATERIAL		SYM	DATE		REVISION