




ELECTRICAL TEST:
 1.100% OPEN SHORT MIS WIRE TEST
 2.CONTACT RESISTANCE:5 OHM MAX
 3.INSULATION RESISTANCE:5M OHM MIN
 4.HI-POT TEST:DC 300V/10ms
 5.PASS 8K@60HZ TEST

CONSUMER ITEM	LENGTH (mm)
4M	4000±30
5M	5000±50



PIN Assignment



NO.	PART NAME	DESCRIPTION	QTY
⑥	CABLE	(1/0.40BC*1P+D1/0.32TC+AL-Foil+ADHESIVE-PET)*5C+1/0.32BC*4C+Filler+AL-Foil+144#/0.12AL BLACK PVC Jacket OD:8.0±0.15mm	m
⑤	SHELL	Black ABS SHELL	2PCS
④	MODEL	Black 45P PVC	g
③	Material	Tinplate	2PCS
②	MODEL	PE,Nature color	g
①	plug	DP M 20P PIN:G/F,SHELL: Gold plated	2PCS

APPROVED	CHECKED	DRAWING	DESIGNED	DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
		YAN	YAN	MODEL NO.		△			
				DRAWING NO.		△			
				FINISHING		△	2021/07/09		A1
				MATERIAL		SYM	DATE		REVISION