



Quality Products. Service Excellence.

Square Hole Cage Nut *CAGNUT Series*



Features

- Cage nuts for square hole rack mounting rails.
- Available in 10-32, 12-24 and M6 mounting profiles.
- Packaged in plastic clamshell or resealable jar (depending on quantity).
- Manufactured in North America.
- TAA Compliant.

Specifications

- Constructed of zinc-plated SAE 1050-1065 spring steel.
- 0.375in (9.54mm) square hole punched panel rails.
- Heat-treated through austempering.
- Recommended torque spec 31.4 +/- 20% inch-lbs
- Maximum load rating will vary depending on rail mounting and cabinet load rating.



Looking for screws as well? Get the **CAGKIT** that includes both screws and cage nuts.



Our legacy 25-pack 1421CNA25 is priced to clear! 80% Off, available while supplies last! The cage nut is identical to the CAGNUT1032 but is the old part number.

Gallery



Accessories

- Rack Screws with Pilot Point
- Cage Nut Installation Tool

10-32 Cage Nuts

Part No.	Qty Included	Package Type	Notes
1421CNA25	25	Clamshell	Over 2,000 available on special
CAGNUT1032-50	50	Plastic Jar	
CAGNUT1032-100	100	Plastic Jar	

12-24 Cage Nuts

Part No.	Qty Included	Package Type
CAGNUT1224-50	50	Plastic Jar
CAGNUT1224-100	100	Plastic Jar

M6 Cage Nuts

Part No.	Qty Included	Package Type	Style
CAGNUTM6-50	50	Plastic Jar	Rear Loading
CAGNUTM6-100	100	Plastic Jar	Rear Loading
1421CNBF100	100	Plastic Jar	Front Loading

Recommended torque spec 60.0 +/- 10% inch-lbs

Tags: **Threaded Adaptors***Data subject to change without notice*

© 2022. Hammond Manufacturing Ltd. All rights reserved.