



ER Type retainers form wire bundles as wires are inserted. Completed bundles then snap out. Two sizes available for 1/2" (12.7mm) and 1 1/4" (31.7mm).

Part Number:	ER.5-E4-X
Product Family:	Elastic Retainers - ER Type
Product Line:	Harness Board Accessories
RoHS Compliancy Status:	RoHS directive is not applicable
Part Description:	Harness Board Elastic Bundle Retainer
Product Type:	Harness Board Accessories
Material:	Nylon 6.6
Color:	Black
Height (In.):	1.00
Height (mm):	25.4
Length (In.):	1.96
Length (mm):	49.8
Width (In.):	.56

Width (mm):	14.2
Arm Material:	ABS
Base Color:	Black
Base Material:	Nylon
Environment:	Indoors
Max. Bundle Diameter (In.):	.50
Max. Bundle Diameter (mm):	12.7
Metric Screw Size:	M2.5
Mounting Method:	Two #4 (M2.5) Screws
Screw Size:	#4 (M2.5)
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	10
Min. Order Qty.:	10