

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2159220800](#)
Status: **Active**
Overview: [Micro-Fit+ Connector System](#)
Description: Micro-Fit+ Plug Housing, Dual Row, 8 Circuits, UL 94V-0, Panel Mount Ears, Glow-Wire Capable, Black

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2159530000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Test Summary 2159530000-TS-000 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	215922
Application	Power, Wire-to-Wire
Overview	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	193264917488

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	1.492/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Product Specification	2159530000-PS-000
Sales Drawing	2159220000-PK-000, 2159220000-SD-000
Test Summary	2159530000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[215922](#) Series

Mates With

Micro-Fit+ Receptacle Housing [206461](#)

Use With

Micro-Fit+ TPA Retainer [206462](#) . Micro-Fit+ Crimp Terminal [215953](#)