

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2140922080](#)
Status: **Active**
Overview: OneBlade 1.00mm-Pitch Wire-to-Board Connector System
Description: OneBlade Receptacle Housing, 1.00mm Pitch, Single Row, Friction Lock, 8 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2140920000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 2140929200-SPK-200 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	214092
Application	Signal, Wire-to-Board
Overview	OneBlade 1.00mm-Pitch Wire-to-Board Connector System
Product Name	OneBlade
UPC	195842620711

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	92.120/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2140929200-SPK-200
Product Specification	2140920000-PS-000
Sales Drawing	2140920000-SD-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214092](#) Series

Mates With

OneBlade Vertical Plug [214094](#) . OneBlade
Right-Angle Plug [214097](#)

Use With

OneBlade Crimp Terminal [214093](#)