

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2181011031](#)
Status: **Active**
Overview: [Micro-Lock Plus Wire-to-Board Connector System](#)
Description: [Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf \(OTS\) Cable Assembly, 2.00mm Pitch, Single Row, 100.00mm Length, 3 Circuits, Black](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	218101
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Lock Plus Both Ends
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock Plus
Type	Discrete Wire Assembly
UPC	195842350168

Physical

Cable Length	100.00mm
Circuits (Loaded)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	2.009/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.50mm
Wire Size AWG	22
Wire/Cable Type	UL 10002

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2181011030-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[218101 Series](#)