

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2181021044

Status:

Active

Overview:

Micro-Lock Plus Wire-to-Board Connector System

Description:

Micro-Lock Plus-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 600.00mm Length, 4 Circuits, Black



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	218102
Assembly Configuration	Single Ended Connector
Connector to Connector	Micro-Lock Plus Both Ends
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock Plus
Type	Discrete Wire Assembly
UPC	195842350540
Physical	
Cable Length	600.00mm
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	10.400/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.50mm
Wire Size AWG	22
Wire/Cable Type	UL 10002
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2181021040-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)10043-DC (17 Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

218102 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION