

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2181021061](#)  
**Status:** **Active**  
**Overview:** [Micro-Lock Plus Wire-to-Board Connector System](#)  
**Description:** [Micro-Lock Plus-to-Pigtail Off-the-Shelf \(OTS\) Cable Assembly, 2.00mm Pitch, Single Row, 100.00mm Length, 6 Circuits, Black](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">218102</a>
Assembly Configuration	Single Ended Connector
Connector to Connector	Micro-Lock Plus Both Ends
Overview	<a href="#">Micro-Lock Plus Wire-to-Board Connector System</a>
Product Name	Micro-Lock Plus
Type	Discrete Wire Assembly
UPC	195842350618

**Physical**

Cable Length	100.00mm
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.290/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.50mm
Wire Size AWG	22
Wire/Cable Type	UL 10002

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2181021060-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[218102 Series](#)