



- Unique design of tie allows it to secure a bundle directly to a chassis or panel without the need for separate fasteners or mounting devices thus reducing costs
- Ties install into pre-drilled hole, go around bunelle, then back out the same hole
- Weather Resistant / Heat Stabilized Nylon 6.6 material

Part Number:	SSPM4HP-L300
Product Family:	<i>Sta-Strap</i> ® Chassis/Panel Mount Tie
Product Line:	Stud Mount and Chassis Mount Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Chassis/Panel Mount Tie, 14.8" Light-Heavy cross section
Product Type:	Cable Ties
Material:	Heat Stabilized Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	Yes
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	Yes

Length (In.):	14.8
Length (mm):	376
Width (In.):	.300
Width (mm):	7.6
CE Compliant:	Yes
Cross Section:	Light-Heavy
Head Height (In.):	.248
Head Height (mm):	6.3
Hole Diameter Range (In.):	.440 – .820
Hole Diameter Range (mm):	11.2 – 21.0
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	4.00
Max. Bundle Diameter (mm):	102
Max. Continuous Use Temperature:	212°F (100°C)
Min. Loop Tensile Strength (Lbs.):	120
Min. Loop Tensile Strength (N):	534
Std. Pkg. UOM:	PK
Thickness (In.):	.062

Thickness (mm):	1.6
Tool:	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50