



Specifications

	PEL00930	PEL00931	PEL00932	PEL00933
Input Voltage	220V AC to 240V AC 50/60Hz			
Nominal Luminous Flux	700lm	1400lm	2100lm	3500lm
Wattage	10W	20W	30W	50W
Beam Angle	120°			
Dimmable	No			
Nominal Lifetime of the Lamp	20,000h			
Light Source	SMD2385			
Colour Temperature	6000K			
Colour Rendering (CRI RA)	≥80			
Warm Up Time (60% Full Light)	Instant Full Light			
Ingress Rating	IP65			
Earthing	Class I			
Weight	0.192kg	0.308kg	0.495kg	0.595kg
Dimension (W×H×D) (mm)	124×95×30	153×117×33	185×139×39	232×175×43

Part Number Table

Description	Part Number
10W LED Floodlight, 700lm, 6000K	PEL00930
20W LED Floodlight, 1400lm, 6000K	PEL00931
30W LED Floodlight, 2100lm, 6000K	PEL00932
50W LED Floodlight, 3500lm, 6000K	PEL00933

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.