



- Used to secure a bundle of wires to another surface such as a control panel, wall or ceiling
- The design allows for bundling before or after screwing clamp in place
- Available in Miniature, Intermediate, Standard and Light-Heavy cross section
- Bundle diameters up to 4.00" (102mm)

Part Number: BC2S-S10-C

Product Family: *Dome-Top®* Barb Ty Clamp Ties

Product Line: Clamp Cable Ties with Steel Barb

RoHS Compliancy Status: Compliant

Part Description: Clamp Tie with metal barb, 8.5", Standard cross section

Product Type: Cable Ties

Material: Nylon 6.6

Color: Natural

CSA Certified: Yes

UL Listed (File #E56854): Yes

UL Recognized (File #E56854): Yes

Length (In.):	8.5
Length (mm):	216
Width (In.):	.185
Width (mm):	4.7
Boss Height (In.):	.160
Boss Height (mm):	4.1
Boss Width (In.):	.400
Boss Width (mm):	10.2
CE Compliant:	Yes
Cross Section:	Standard
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	2.00
Max. Bundle Diameter (mm):	51
Max. Continuous Use Temperature:	185°F (85°C)
Metric Screw Size:	M5
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Nominal Hole Diameter (In.):	.200

Nominal Hole Diameter (mm):	5.1
Screw Size:	#10
Std. Pkg. UOM:	PK
Thickness (In.):	.052
Thickness (mm):	1.3
Tool:	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100