



- Used to secure a bundle of wires to another surface such as a control panel, wall or ceiling
- The design allows for bundling before or after screwing clamp in place
- Available in Miniature, Intermediate, Standard and Light-Heavy cross section
- Bundle diameters up to 4.00" (102mm)

Part Number: BC4LH-S25-L

Product Family: *Dome-Top*® Barb Ty Clamp Ties

Product Line: Clamp Cable Ties with Steel Barb

RoHS Compliancy Status: Compliant

Part Description: Clamp Tie with metal barb, 15.5", Light-Heavy cross section

Product Type: Cable Ties

Material: Nylon 6.6

Color: Natural

CSA Certified: Yes

UL Listed (File #E56854): Yes

UL Recognized (File #E56854): Yes

Length (In.):	15.5
Length (mm):	394
Width (In.):	.275
Width (mm):	7.0
Boss Height (In.):	.265
Boss Height (mm):	6.7
Boss Width (In.):	.520
Boss Width (mm):	13.2
CE Compliant:	Yes
Cross Section:	Light-Heavy
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	4.00
Max. Bundle Diameter (mm):	102
Max. Continuous Use Temperature:	185°F (85°C)
Metric Screw Size:	M6
Min. Loop Tensile Strength (Lbs.):	120
Min. Loop Tensile Strength (N):	534
Nominal Hole Diameter (In.):	.260

Nominal Hole Diameter (mm):	6.6
Screw Size:	1/4
Std. Pkg. UOM:	PK
Thickness (In.):	.065
Thickness (mm):	1.7
Tool:	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50