



Innovative solution for managing Network Cabling

- **Exclusive** material with hooks and loops on the same side allows user to secure a greater range of bundle diameters, including smaller bundles
- Low profile contoured cinch ring reduces overall bundle size
- Soft hook and loop material maintains network data integrity by protecting against over-tensioning, unraveling and delamination
- New colors available to match your application needs
- Releasable and reusable hundreds of times which is ideal for applications requiring frequent moves, adds or changes
- Tapered tip facilitates easy, snag-free threading to speed installation time
- Brass grommet (on UGCTC and UGCTE styles) assures reliable installations with a high strength metal grommet that resists pull-out

Note: Minimum 2" overlap required to achieve loop tensile rating.

Part Number:	UCT3S-X6
Product Family:	<i>Ultra-Cinch</i> ™ Hook & Loop Ties
Product Line:	Hook and Loop Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Ultra-Cinch Hook & Loop Tie, Cinch style, 12.0" length, Standard cross section
Product Type:	Same-sided Cinch Ties
Material:	Nylon Hook & Loop, Nylon Cinch Ring
Color:	Blue

CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	No
Length (In.):	12.0
Length (mm):	305
Width (In.):	.850
Width (mm):	21.6
CE Compliant:	Yes
Cross Section:	Standard
Head Height (In.):	.450
Head Height (mm):	11.4
Head Width (In.):	1.100
Head Width (mm):	27.9
Locking Style:	Releasable
Max. Bundle Diameter (In.):	3.00
Max. Bundle Diameter (mm):	76
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Std. Pkg. UOM:	PK

Thickness (In.): .100

Thickness (mm): 2.5

UOM: PC

Std. Pkg. Qty.: 10

Min. Order Qty.: 10