

PRO-ELEC



Solar Garden Light Model: PEL01355

Please read these instructions carefully before use and retain for future reference.

IMPORTANT SAFETY INFORMATION

- Avoid locations of high temperature or humidity.
- The lamp is constructed to IP65 suitable for outdoor use.

WHAT'S INCLUDED

- Lamp assembly.
- User manual.

INSTALLATION

- Installation is simply embedding the spike in the ground then fit the lamp assembly to the top, ensuring the solar panel is exposed for maximum charging efficiency but not in the vicinity of other artificial light source or the low light illumination may not function.

OPERATION

- **Allow at least 8hrs for the battery to fully charge initially.**

NOTE: the lamp does not light except in low ambient light levels.

- Remove the lamp from the spike, and rotate and remove the lens.
- Remove the battery insulating strip then refit the lens and replace the lamp onto the spike.
- When the ambient light falls below a preset level the LEDs will illuminate constantly.

CLEANING & MAINTENANCE

- Clean the unit only with a damp cloth. Do not use any chemicals, abrasives or solvents that could damage the casing or lens.
- During periods where the lamp may not be used, it is advisable to charge the battery occasionally to maintain it's performance and before re-using the lamp.

SPECIFICATION

Solar panel: Monocrystal 2V, 0.32W

Battery: 1 x AA Ni-MH 600mAh rechargeable.

LED: 1 x white FT5mm

Working time: up to 8 hours.

Dimensions: DIA120 x H420mm.



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China
PO Box 13362 Dublin 2
PR2 9PP
Man Rev 1.1