

## Han 48B-HBM-SL-CP



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 048 0321
Specification	Han 48B-HBM-SL-CP
HARTING eCatalogue	<a href="https://b2b.harting.com/09300480321">https://b2b.harting.com/09300480321</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With thermo-plastic cover incl. flat seal
Type	Low construction

### Version

Size	48 B
Locking type	Single locking lever
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR



Pushing Performance

## Material properties

Material (locking)	Stainless steel
--------------------	-----------------

## Specifications and approvals

Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	654 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440202 Shell for industrial connectors