



- Economical series of tools for maintenance or construction applications
- Operator-controlled tension and cut-off:
(STS2/STH2/ST3EH) Install cable tie around bundle and tension tie by squeezing tool handle. Reduce tension slightly and twist tool 1/4 turn either direction to cut off excess cable tie.
(STHV) Install cable tie around bundle and tension tie by squeezing tool handle. A separate lever cuts off excess cable tie.
- Excellent tool for low volume applications
- Use with the full line of *PANDUIT*® Cable Ties

Part Number: STH2
Product Family: Cable Tie Tools – Installer Controlled Tension and Cut-Off
Product Line: Manual Cable Tie Installation Tools

RoHS Compliancy Status: RoHS directive is not applicable

Part Description: Installs Standard, Heavy-Standard, Light-Heavy and Heavy cross section cable ties. Inexpensive, maintenance-free, all purpose tool. Ergonomic handle design and short handle span. Top loading feature for right or left-handed users.

Color Identification: Red
Weight: 2.5 oz. (71g)

Color: Red

Part Features: Ergonomic handle design, short handle span and top loading feature for right or left handed users. Red color.

Std. Pkg. UOM: EA

Used With Cable Ties: S, HS, LH, H

Weight (g): 71

Weight (oz.): 2.5

UOM: PC

Std. Pkg. Qty.: 1

Min. Order Qty.: 1