

## Product information

# 02 02 180

## High Leverage Combination Pliers

DIN ISO 5746



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



General	
Article No.	02 02 180
EAN	4003773034896
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	240 g
Dimensions	180 x 47 x 22 mm
Standard	DIN ISO 5746
Reach	no
RohS	no

Technical details	
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacities piano wire (diameter)	Ø 2.0 mm
Cutting capacity copper cable, multiple-stranded	Ø 11.5 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm <sup>2</sup>

Classification	
eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted

