

Product information

11 06 160 T

Insulation Stripper

With opening spring, universal

IEC 60900 DIN EN 60900

- Pliers with integrated, insulated tether attachment point for a tool tether
- For single, multiple and fine stranded conductors with plastic or rubber insulation up to Ø 5.0 mm or 10 mm²
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Special tool steel, forged, oil-hardened



⚠ 1000 V 



General

Article No.	11 06 160 T
EAN	4003773081418
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	180 g
Dimensions	160 x 100 x 27 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Stripping capacities in square millimetres	10 mm ²
Stripping capacities (diameter)	Ø 5.0 mm
AWG	8
Drop Protection System	yes
VDE tested	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510

Spare Parts

11 09 01	Set of spare parts (screw and nut) for 11 XX 160,
----------	---

technical change and errors excepted

