

## Product information

# 34 52 130 ESD

## Precision Electronics Gripping Pliers ESD

DIN ISO 9655 DIN EN 61 340-5




- The assortment for highest standard of performance and results
- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Bolted joint: precise, zero backlash operation of pliers
- Precisely finished joint surfaces for smooth, low friction movement along the complete opening range
- Low-friction double spring for gentle and even opening
- With precision laser cut cross-shaping
- Non-reflective finish
- Low weight
- Ergonomically shaped, two-colour dual component ESD handles, black/grey
- Half-round jaws
- With precision laser cut cross-shaping
- Ball bearing chrome steel, forged, multi stage oil-hardened



General	
Article No.	34 52 130 ESD
EAN	4003773080305
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	130 x 51 x 20 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
Reach	no
RohS	no

Technical details	
Jaw length (B)	22.7 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.6 mm
Tips thickness (F)	1.6 mm
Head width (A)	11.2 mm
ESD	yes



**Classification**

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

*technical change and errors excepted*

