

Product information

35 82 145

Electronics Pliers

DIN ISO 9655



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- 45° bent, half-round, long jaws
- Ball bearing chrome steel, oil hardened




General

Article No.	35 82 145
EAN	4003773039396
Head	mirror polished
Handles	with multi-component grips
Weight	102 g
Dimensions	145 x 59 x 19 mm
Standard	DIN ISO 9655
Reach	no
RohS	no

Technical details

Jaw length (B)	35.0 mm
Jaw thickness (joint) (D)	7.5 mm
Tips width (E)	2.5 mm
Tips thickness (F)	1.0 mm
Head width (A)	12.0 mm
Dimensions angle	45 °





Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112104

Spare Parts

35 99 01	Spare spring for electronics pliers, (2x)
----------	---

technical change and errors excepted