

## Product information

# 46 20 A61

## Circlip Pliers

For external circlips on shafts

DIN 5254 B



∠90°

- With locking device, can be released
- With replaceable tips made of tempered steel
- Black powder-coated
- DIN 5254 B; 90° angled tips
- Pliers body: rolled steel, high-strength
- Tips: special tool steel, oil-hardened

### General

|             |                     |
|-------------|---------------------|
| Article No. | 46 20 A61           |
| EAN         | 4003773025030       |
| Pliers      | black powder-coated |
| Weight      | 1,826 g             |
| Dimensions  | 580 x 151 x 17 mm   |
| Standard    | DIN 5254 B          |
| Reach       | no                  |
| RohS        | no                  |

### Technical details

|                 |                |
|-----------------|----------------|
| Size of shaft   | Ø 252 – 400 mm |
| Tips (diameter) | 4.5 mm         |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| ETIM 5.0       | EC002228   |
| ETIM 6.0       | EC002228   |
| proficl@ss 6.0 | AAC470c002 |
| UNSPSC 13.1    | 27112140   |

### Spare Parts

|           |                                     |
|-----------|-------------------------------------|
| 46 29 A61 | 1 pair of spare tips for 46 20 A61, |
|-----------|-------------------------------------|

technical change and errors excepted