

Product information

70 06 160 T

Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900



⚡ 1000 V 

- With elongated cutting edge
- Pliers with integrated, insulated tether attachment point for a tool tether
- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	70 06 160 T
EAN	4003773081463
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	230 g
Dimensions	160 x 54 x 28 mm
Standard	DIN ISO 5749 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.0 mm
Cutting capacities hard wire (diameter)	Ø 2 mm
Drop Protection System	yes
VDE tested	yes

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted



clean cutting of thin copper wires, also at the cutting edge tips