

Product information

71 02 200 T

KNIPEX CoBolt®

Compact Bolt Cutter



Clever muscle man

- Micro-structured cutting edge reduces slipping of the material from the jaws
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- With slim multi-component grips without collar for better handling and easier transport
- With large contact surface on the handles for better allotment of pressure and more comfort at work
- Pliers with tether attachment point for mounting a fall protection system
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to Ø 5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

| | |
|-------------|--|
| Article No. | 71 02 200 T |
| EAN | 4003773080046 |
| Pliers | black atramentized |
| Handles | with slim multi-component grips, with integrated tether attachment point for a tool tether |
| Weight | 375 g |
| Dimensions | 200 x 51 x 23 mm |
| Reach | yes |
| RohS | no |

Technical details

| | |
|--|----------|
| Cutting capacities soft wire (diameter) | Ø 6 mm |
| Cutting capacities medium hard wire (diameter) | Ø 5.2 mm |
| Cutting capacities hard wire (diameter) | Ø 4.0 mm |
| Cutting capacities piano wire (diameter) | Ø 3.6 mm |
| Drop Protection System | yes |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC002689 |
| ETIM 6.0 | EC002689 |
| proficl@ss 6.0 | AAC440c002 |
| UNSPSC 13.1 | 27111512 |

technical change and errors excepted



with gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm