

## Product information

# 71 72 610

## Bolt Cutter



### Cuts hard components up to 48 HRC

- Cutting capacity up to 48 HRC hardness
- Robust cutting edges are additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged-in stopper with comfortable shock-absorber
- Good access due to very flat construction of head and joint area
- Ergonomically angled handles to minimise effort
- Sturdy non-slip two-colour multi-component handle sleeves
- Precise adjustment (12 positions) by eccentric bolt
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Bolted cutter head, replaceable
- Joint: special tool steel, forged
- Handles: steel tube, powder-coated
- Blade: chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	71 72 610
EAN	4003773066767
Head	grey atramentized
Handles	with multi-component grips
Weight	2,550 g
Dimensions	610 x 122 x 34 mm
Reach	no
RohS	no
Technical details	
HRC 19	Ø 9 mm
HRC 40	Ø 8 mm
HRC 48	Ø 7 mm
Cutting edge length mm	34 mm
Head thickness	33 mm
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512
Spare Parts	
71 79 610	Spare cutter head for 71 72 610 complete with screws,

technical change and errors excepted

