

Product information

74 02 140

High Leverage Diagonal Cutter

DIN ISO 5749

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

| | |
|-------------|----------------------------|
| Article No. | 74 02 140 |
| EAN | 4003773042419 |
| Pliers | black atramentized |
| Head | polished |
| Handles | with multi-component grips |
| Weight | 157 g |
| Dimensions | 140 x 48 x 20 mm |
| Standard | DIN ISO 5749 |
| Reach | no |
| RohS | no |

Technical details

| | |
|--|----------|
| Cutting capacities medium hard wire (diameter) | Ø 3.1 mm |
| Cutting capacities hard wire (diameter) | Ø 2.0 mm |
| Cutting capacities piano wire (diameter) | Ø 1.5 mm |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC000165 |
| ETIM 6.0 | EC000165 |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1 | 27112114 |

technical change and errors excepted

