

Product information

81 13 250

Siphon and Connector Pliers

DIN ISO 8976



Now with more grip: increased grip on the workpiece thanks to two-component plastic inserts

- Fine adjustment for ideal adjustment to diverse diameters up to 75 mm
- For connectors, oil filters, plastic pipes and siphons
- Ideal for tightening and loosening siphon screw connections, plastic pipe fittings and round union nuts
- With exchangeable plastic jaws for sensitive surfaces; up to Ø 75 mm
- For connectors and couplings with screw connection, such as Cannon circular connectors
- For gentle loosening of hoses on nozzles and filter cartridges
- Optimum adhesion on dirt-, oil- and fatfree surfaces
- 25-way adjustable box joint
- Ergonomic handle geometry
- Changeable gripping jaws with two-component plastic insert with a hard carrier component (red) and a soft adhesive component (blue)
- Chrome vanadium electric steel, forged, oil-hardened



General

Article No.	81 13 250
EAN	4003773078494
Pliers	chrome-plated
Head	chrome-plated
Handles	with non-slip plastic coating
Weight	345 g
Dimensions	250 x 60 x 17 mm
Standard	DIN ISO 8976
Reach	no
RohS	no

Technical details

Working Capacity (diameter)	Ø 10 – 75 mm
Adjustment positions	25

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002211
ETIM 6.0	EC002211
proficl@ss 6.0	EAD318c001
UNSPSC 13.1	27112112

Spare Parts

81 19 250 V01	2 pairs of plastic inserts 1C for 81 11 250 / 81 13 250,
81 19 250 V02	2 pairs of plastic inserts 2C for 81 11 250 / 81 13 250,

technical change and errors excepted





