

Product information

83 61 015

Pipe Wrench S-Type

With fast adjustment

- Pinch guard prevents operators' fingers being pinched
- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Maximum load capability thanks to completely hardened handles
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 61 015
EAN	4003773077619
Pliers	grey powder-coated
Handles	plastic coated
Weight	1,470 g
Dimensions	420 x 84 x 28 mm
Reach	no
RohS	no

Technical details

Clamping width	60 mm
Capacities for pipes (diameter)	Ø 2 3/8 Inch
Capacities for pipes (diameter)	Ø 60 mm
Capacities for nuts	60 mm
Inner diameter, inches	Ø 1 1/2 Inch
Pipe inner dia.	37.5 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

technical change and errors excepted

