

Product information

83 61 020

Pipe Wrench S-Type

With fast adjustment

- Pinch guard prevents operators' fingers being pinched
- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Maximum load capability thanks to completely hardened handles
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 61 020
EAN	4003773078876
Pliers	grey powder-coated
Handles	plastic coated
Weight	2,480 g
Dimensions	560 x 94 x 32 mm
Reach	no
RohS	no
Technical details	
Capacities for pipes (diameter)	Ø 2 3/4 Inch
Capacities for pipes (diameter)	Ø 70 mm
Capacities for nuts	70 mm
Inner diameter, inches	Ø 2 Inch
Pipe inner dia.	50 mm
Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

technical change and errors excepted

