

Product information

87 05 300

KNIPEX Cobra®

High-tech Water Pump Pliers

DIN ISO 8976

- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

| | |
|-------------|----------------------------|
| Article No. | 87 05 300 |
| EAN | 4003773014126 |
| Pliers | grey atramentized |
| Head | polished |
| Handles | with multi-component grips |
| Weight | 580 g |
| Dimensions | 300 x 48 x 16 mm |
| Standard | DIN ISO 8976 |
| Reach | no |
| RohS | no |

Technical details

| | |
|---------------------------------|--------------|
| Adjustment positions | 30 |
| Capacities for nuts | Ø 2 3/4 Inch |
| Capacities for nuts | 60 mm |
| Capacities for pipes (diameter) | Ø 70 mm |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000164 |
| ETIM 6.0 | EC000164 |
| proficl@ss 6.0 | AAA936c004 |
| UNSPSC 13.1 | 27112112 |

Spare Parts

| | |
|----------|------------------------------------------------------------------------------------|
| 87 09 01 | Assortment of spare parts for adjustment for 86/87 XX 250/300 (without 87 2X XXX), |
|----------|------------------------------------------------------------------------------------|

technical change and errors excepted



