

Product information

89 01 250

Water Pump Pliers

With groove joint

DIN ISO 8976

- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Non-slip joint
- Jaw profile designed to fit screws and nuts
- Joint design reduces strain of the centre bolt, hence no wear on pivot
- Pinch guard prevents operators' fingers being pinched
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC for tool length 250 mm: high wear resistance and stable gripping
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	89 01 250
EAN	4003773023067
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	325 g
Dimensions	250 x 50 x 20 mm
Standard	DIN ISO 8976
Reach	no
RohS	no
Technical details	
Capacities for pipes (diameter)	Ø 1 5/16 Inch
Capacities for pipes (diameter)	Ø 34 mm
Capacities for nuts	36 mm
Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112
Spare Parts	
89 09 250 01	Joint screw for 89 01 250,
89 09 250 02	Hexagonal nut for 89 01 250,

technical change and errors excepted